

Openable along the inner radius, cost-effective





e-chains® | Series 074 | Openable along the inner radius from one side with film hinge


Part No. e-chains®	Bi [mm]	Ba [mm]	R Available bend radii [mm]	Weight [kg/m]
074. 06 .R.0	06	12.3	018 028 038	≈ 0.14
074. 10 .R.0	10	16.3	018 028 038	≈ 0.15
074. 16 .R.0	16	22.3	018 028 038	≈ 0.16
074. 20 .R.0	20	26.3	018 028 038	≈ 0.17

Complete Part No. with required radius (R). Example: 074.10.018.0

Installation dimensions




Inner height [mm]	11.5
Pitch [mm/link]	20
Links/m	50
corresponds to [mm]	1,000
e-chain® length	$L_K = S/2 + K$



R	018	028	038
H	51	71	91
D	56	66	76
K	100	130	160


The required clearance height: $H_F = H + 10\text{mm}$ (with 0.2kg/m fill weight)292 More information ► www.igus.eu/074

Mounting brackets, polymer one-piece | Locking



Width index	Part No. full set with tiewrap plates	Part No. full set without tiewrap plates	A [mm]	B [mm]	Number of teeth
06. ►	060.06.12PZ	060.06.12	—	12.5	1
10. ►	060.10.12PZ	060.10.12	—	16.5	1
16. ►	060.16.12PZ	060.16.12	—	22.5	2
20. ►	060.20.12PZ	060.20.12	—	27	2

Material mounting bracket - igumid G, temperature: -40° up to +120°C, VDE 0304 IIC UL94-HB



060.10.12PZ.A1 Order example

.A... to indicate option with brackets pre-fitted

With integrated strain relief tiewrap plates

Full set

Series

igus 3D CAD, service life calculation, configurators and more ► www.igus.eu/E2micro

293